


Single-Use Coriolis Mass Flow Meter



Benefits

- Gamma Sterilizable PEEK Sensor
- USP Class VI wetted surfaces
- Designed for single-use biopharm processing applications



US Patents 8,404,076 & 8,887,578. Japanese Patent 5,602,884
Other patents pending.

Malema's SumoFlo® CPFM-8100 series Single-Use Coriolis Meter is specifically designed for measuring liquids in biopharmaceutical and other applications that require all gamma-sterilizable wetted surfaces. The fluid contacting surfaces are made of unreinforced polyether ether ketone (PEEK) that meets USP Class VI, USP 661, and USP 788 standards.

Fluid flows into the sensor consisting of two flow sensitive elements which are vibrated relative to one another – similar to the tines of a tuning fork. Fluid interacts with the sensor dynamically in such a way that the sensor's response is immune to the fluid's chemical and physical properties, flow regime, or variations in flow velocity profile. Fluid mass flow rate is determined by measuring the relative motion of the vibrating flow sensitive elements.

Features

- Accuracy: $\pm 1\%$ of flow reading; unaffected by flow regime or variations to the velocity profile
- Fluid measurement performance is independent of fluid properties

Applications

- Tangential Flow Filtration
- Depth Filtration
- Chromatography
- Buffer Dilution
- Pure water or ultra high purity chemicals
- Fluids with varying density or viscosity

Measurement Specifications

Model CSEN-8100-C	-031	-062	-063	-082	-152	-153
Accuracy	±1% of rate for 10% to 100% of full scale rated flow rate ±(1% of rate + Z.O.S) for < 10% of full scale rated flow rate					
Temperature	Ambient: 0-50°C Fluid: 4-40°C					
Operating Pressure	80 psig (max.)					
Flow Range	50 – 1,500 g/min	500 – 5,000 g/min	900 – 9,000 g/min	2 - 20 kg/min	7.5 – 75 kg/min	10 – 100 kg/min
Zero Offset Stability (Z.O.S.)	0.75 g/min	2 g/min	4 g/min	10 g/min	20 g/min	40 g/min

Material Specifications

Model CSEN-8100-C	-031	-062	-063	-082	-152	-153
Process Connections *	1/8" barb	1/4" barb	3/8" barb	1/2" barb	3/4" barb	1" barb
Wetted Materials	Unreinforced PEEK (Polyether ether ketone), Polysulfone (for temperature sensor only), Stainless Steel (for temperature sensor only), Adhesive compliant with ISO 10993. All polymeric wetted materials are USP Class VI compliant.					
Interconnecting Cable Length	Standard 3 m; Maximum up to 30 m					
Ingress Rating For Connectors	IP65					

* Consult the factory for other types of process connection options.

Electrical Specifications

Supply Voltage	24 VDC ±10%
Power Consumption	Max 6 W
Programming	Operator Parameter configuration through configuration port with a PC
Analog Output Module	4–20 mA
Digital Input/Output Module	Configurable as Frequency or Digital I/O
Frequency Output	0 to 10 kHz proportional to flow rate
Digital Output over MODBUS *	Mass Flow Rate, Volumetric Flow Rate, Density, Temperature **

* Requires CELE-8100 model configured for MODBUS communications.

** Requires CELE-8100 and CSEN-8100 models configured for temperature compensation.

Certifications/Compliances

USP Class VI Material Certification	CE Compliance via the following testing: 1. EN61000-4-2: Electrostatic Discharge 2. EN61000-4-3: Radiated Immunity (and Radiated Emissions) 3. EN61000-4-4: Electrical Fast Transients 4. EN61000-4-5: Surge – Power Line 5. EN61000-4-6: Conducted Immunity
USP 661 for Containers/Plastics	
USP 788 for Containers/Plastics	
Directive 2011/65/EU (RoHS)	

© 2017 Malema Engineering Corporation. All rights reserved.

Malema Sensors and SumoFlo are registered trademarks of Malema Engineering Corporation. Malema Engineering Corporation, Malema, the Malema logo and the SumoFlo logo are trademarks of Malema Engineering Corporation. All other trademarks are property of their respective owners.

Malema supplies this publication for informational purposes only. While every effort has been made to ensure accuracy, this publication is not intended to make performance claims or process recommendations. Malema does not warrant, guarantee, or assume any legal liability for the accuracy, completeness, timeliness, reliability, or usefulness of any information, product, or process described herein. We reserve the right to modify or improve the designs or specifications of our products at any time without notice. For actual product information and recommendations, please contact your local Malema representative.

Corporate Headquarters
1060 S Rogers Circle
Boca Raton, FL 33487

P: (561) 995-0595 F: (561) 995-0622

West Coast Headquarters
2329 Zanker Road
San Jose, CA 95131

P: (408) 970-3419 F: (408) 970-3426

Asia Pacific Headquarters
35 Marsiling Industrial Estate 3, Unit #02-06
Singapore 739257

P: (65) 6482-3533 F: (65) 6484-4231